


**80/20 Expands Selection of Polycarbonate and Wire Mesh Panels!**

**NEW!**

**Polycarbonate Panels - Now Available in 3 New Thicknesses**

- Mount 3/8" or 1/2" thick plastic panels in the T-slot with rubber gasket
- For cut-to-size services for plastic panels thicker than 1/4", see Section 12 of the 80/20 catalog




Part No.	Trade Name	Color	Thickness	Load	Stock Sheet Size
2645	Lexan <sup>®</sup> / Makrolon <sup>®</sup>	Clear	.500"	3.120 lbs./sq. ft.	48" x 96" + .875 - 0
2644	Lexan <sup>®</sup> / Makrolon <sup>®</sup>	Clear	.375"	2.340 lbs./sq. ft.	48" x 96" + .875 - 0
2643	Lexan <sup>®</sup> / Makrolon <sup>®</sup>	Clear	.118"	.737 lbs./sq. ft.	48" x 96" + .875 - 0
65-2645	Lexan <sup>®</sup> / Makrolon <sup>®</sup>	Clear	12.7mm	15.235 kg./sq. meter	1219.2 x 2438.4mm
65-2644	Lexan <sup>®</sup> / Makrolon <sup>®</sup>	Clear	9.5mm	11.425 kg./sq. meter	1219.2 x 2438.4mm
65-2643	Lexan <sup>®</sup> / Makrolon <sup>®</sup>	Clear	3mm	3.662 kg./sq. meter	1219.2 x 2438.4mm

**NEW!**

**Wire Mesh Panels - Now Available in Powder Coated Blue and Black**

- Low-cost alternative to expanded metal panels
- Lightweight yet impact resistant
- Powder coat finish



Part No.	Material	Wire Gauge	Thickness	Load	Dimensions	Stock Sheet Size
2468	Powder Coated Blue	12	.200"	1.010 lbs./sq. ft.	Square 1" x 1"	48" x 96" +/- .50"
2479	Powder Coated Black	12	.200"	1.010 lbs./sq. ft.	Square 1" x 1"	48" x 96" +/- .50"
65-2468	Powder Coated Blue	12	5.10mm	4.93 kg./sq. meter	Square 25.40 x 25.40mm	1219.2 x 2438.4mm
65-2479	Powder Coated Black	12	5.10mm	4.93 kg./sq. meter	Square 25.40 x 25.40mm	1219.2 x 2438.4mm

**NEW!**

**PVC Coated Wire Mesh Panels - Now Available in 2" x 2" Dimensions**

- Widely used in guarding and enclosure applications
- Strong yet lightweight
- Low wear value, won't flake or chip
- Corrosion-resistant and light impact-resistant



Part No.	Material	Wire Gauge	Thickness	Load	Dimensions	Stock Sheet Size
2478	PVC Coated Carbon Steel Black	12	.210"	1.300 lbs./sq. ft.	Square 2" x 2"	48" x 96" +/- .50"
65-2478	PVC Coated Carbon Steel Black	12	5.30mm	6.348 kg./sq. meter	Square 50.80 x 50.80mm	1219.2 x 2438.4mm